

Dual Q smoke alarm device incl. 230 V base

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2337 02	1	84.80	03	4010337033080

Increased quality criteria and technical advancements in smoke alarm devices are indicated on the market with the new Q test mark. The new Q-Label is an autonomous, manufacturer-independent quality mark for high-quality smoke alarm devices which undergo special testing for long-term use. The latest generation of Gira smoke alarm devices fulfil the criteria of the new Q-Label quality mark. The smoke alarm devices operate based on the photoelectric scattered light principle without radioactive particles. The smoke alarm devices detect smoke accumulation early and emit a warning signal before the concentration of smoke can become hazardous to people. Alerting occurs via a loud pulsing alarm tone and a flashing LED.

Features

- Only for use in private residential units or residential-like areas in accordance with DIN 14676.

Q-Label

- Tested durability and reduction of false alarms.
- Increased stability, e.g. against external factors.
- Permanently installed battery with a service life of up to 10 years.
- designAccording to DIN EN 14604.
- KRIWAN approval.
- Dual Q smoke alarm device with mains power (230 V) for private home use. This item does not need a mounting plate.
- The base with integrated power supply unit is used to provide the Dual Q smoke alarm device with mains voltage (230 V).
- The supply cable/networking cable is connected in the base. Contact is automatic when the smoke alarm device is mounted.
- The battery in the Dual Q smoke alarm device automatically takes over the power supply in the event of a mains failure.
- Up to 40 smoke alarm devices can be networked via a separate conductor.

=

Technical data

Power supply:	Via smoke alarm device battery
Battery life:	up to 10 years (following activation)
Acoustic signal:	Alarm: at least 85 dB (A)
Optical signal:	Ring indicator (red LED)

Ambient temperature:	-5 °C to +55 °C
Installation height:	Max. 6 m
Protection class:	IP30
Area of application:	DIN 14676
Standards:	DIN 14604
- design:	A
Power supply:	AC 230 V, 50 Hz via base
Battery:	back-up only
- Type:	U9VL-J-P
- UN no.:	3091
Battery life:	at least 10 years
Acoustic signal	
- Alarm:	at least 85 dB (A)
- Function test:	approx. 75 dB (A)
Optical signal	
- Base:	Green LED (230 V)
- Ring indicator:	Red LED indicates status and malfunctions
Weight:	approx. 350 g

Dimensions in mm

Housing:	Ø 125	H 77
----------	-------	------
