

System 3000 universal LED dimmer Mini

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2440 00	1/5	88.06	02	4010337031390

Features

- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen or LED lights, dimmable inductive transformers for halogen or LED lights, HV LED or compact fluorescent lamps.
- Operation via auxiliary units.
- Automatic or manual setting of dimming principle according to load (leading or trailing edge).
- Display of the selected operating mode using LED.
- Switch-on function that preserves the life of the lamp.
- Switch-on brightness can be saved permanently.
- Switch on with the last brightness set, or a saved switch-on brightness.
- Minimum brightness can be set.
- Electronic short-circuit protection.
- Electronic excess-temperature protection.
- Operation with or without a neutral conductor connection.

Technical data

Rated voltage: AC 230 V, 50/60 Hz

Standby: max. 0.3 W

Connected load at 25 °C

- HV LED lamps (leading edge): typically 3 to 50 W
- HV LED lamps (trailing edge): typically 3 to 100 W
- Compact fluorescent lamp: typically 3 to 50 W
- Light bulbs: 20 to 210 W
- HV halogen lamps: 20 to 210 W
- Tronic transformers: 20 to 210 W
- Electronic transformer with LV LED (leading edge): typically 20 to 50 W
- Electronic transformer with LV LED (trailing edge): typically 20 to 100 W
- Wound electronic transformer: 20 to 210 VA
- Wound transformer with NV-LED: typically 20 to 50 VA

Auxiliary units

- Non-illuminated mechanical push buttons: unlimited

- 2-wire auxiliary insert:	unlimited
- 3-wire auxiliary insert:	10
Cable length	
- Auxiliary unit:	Max. 100 m
- Load:	Max. 100 m
Installation:	in device box pursuant to DIN 49073, in combination with a suitable cover
Connection cross section	
- Single-wire:	Max. 4 mm ²
- Fine-wire without core jacket:	Max. 4 mm ²
- fine-wire with core jacket:	Max. 2.5 mm ²
Ambient temperature:	-5 °C to +45 °C

Notes

- In principle, it is possible to operate the dimmer without connecting the neutral conductor, but some LED and CFLi light sources make the neutral conductor connection necessary to avoid flickering.
 - Operation without a neutral conductor increases the minimum load for light bulbs, HV halogen lamps, Tronic transformers and wound transformers to 50 W.
 - Electronic transformers and ballast devices for LED lamps can be operated with the dimming procedure specified by the manufacturer.
 - The switch-on brightness cannot be saved using a button.
 - The installation adapter mini housing is used for installation in false ceilings 5429 00.
 - If the ambient temperature is higher than 25 °C, the connected load must be reduced.
-

Dimensions in mm

Ø 48 H 19,5
