

System 3000 universal LED rotary dimming insert Komfort

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---------------|-----------|--------------|------------------------|----|---------------|
| | 2455 00 | 1/5 | 108.86 | 02 | 4010337031413 |

Features

- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen or LED lights, dimmable inductive transformers for halogen or LED lights, HV LED or compact fluorescent lamps.
- Connecting auxiliary units is possible.
- Automatic or manual setting of dimming principle according to load (leading or trailing edge).
- Display of the selected operating mode using LED.
- Switch-on function that preserves the life of the lamp.
- Switch-on brightness can be saved permanently.
- Switch on with the last brightness set, or a saved switch-on brightness.
- Hotel-card function can be activated: Light switches "On" following power interruption (from index 01).
- Minimum brightness can be set.
- Electronic short-circuit protection.
- Electronic excess-temperature protection.
- Operation with or without a neutral conductor connection.

Technical data

Rated voltage: AC 230 V, 50/60 Hz

Standby: max. 0.35 W

Connected load at 25 °C

- HV LED lamps (leading edge): typically 3 to 100 W
- HV LED lamps (trailing edge): typically 3 to 400 W
- Compact fluorescent lamp: typically 3 to 100 W
- Light bulbs: 20 to 420 W
- HV halogen lamps: 20 to 420 W
- Tronic transformers: 20 to 420 W
- Electronic transformer with LV LED (leading edge): typically 20 to 100 W
- Electronic transformer with LV LED (trailing edge): typically 20 to 200 W
- Wound electronic transformer: 20 to 420 VA
- Wound transformer with NV-LED: typically 20 to 100 VA

Auxiliary units

- Non-illuminated mechanical push buttons: unlimited

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/20.

| | |
|----------------------------------|-------------------------------------|
| - 2-wire auxiliary insert: | unlimited |
| - 3-wire auxiliary insert: | max. 10 |
| Cable length | |
| - Auxiliary unit: | Max. 100 m |
| - Load: | Max. 100 m |
| Installation: | in device box pursuant to DIN 49073 |
| Installation depth: | 24 mm |
| Connection cross section | |
| - Single-wire: | Max. 4 mm ² |
| - Fine-wire without core jacket: | Max. 4 mm ² |
| - fine-wire with core jacket: | Max. 4 mm ² |
| Ambient temperature: | -5 °C to +45 °C |

Notes

- In principle, it is possible to operate the dimmer without connecting the neutral conductor, but some LED and CFLi light sources make the neutral conductor connection necessary to avoid flickering.
 - Operation without a neutral conductor increases the minimum load for light bulbs, HV halogen lamps, Tronic transformers and wound transformers to 50 W.
 - Electronic transformers and ballast devices for LED lamps can be operated with the dimming procedure specified by the manufacturer.
 - If the ambient temperature is higher than 25 °C, the connected load must be reduced.
-