

UPS for emergency set

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|-------------------|-----------|--------------|------------------------|----|---------------|
| pure white glossy | 2918 03 | 1/5 | 231.03 | 34 | 4010337011767 |

Features

- Uninterruptible power supply for the Gira emergency set.
- If the mains input voltage drops or fails, the connected load continues to be supplied by the rechargeable battery without interruption.
- If the mains input voltage increases or is restored, the rechargeable battery is disconnected from the load and recharged in normal mains operation.
- The signal contact (M) can be used to signal the operating statuses "UPS active" or "Rechargeable battery defective".

Technical data

| | |
|--|--|
| Input voltage: | DC 24 V |
| Output voltage in rechargeable battery operation: | 22.8 V \pm 10% |
| Rated load in rechargeable battery operation: | 130 mA for 1 h |
| Maximum load - in rechargeable battery operation: | 300 mA for 15 min |
| Battery/rechargeable battery - Type: - UN no.: | UR18500F 3480 |
| Maximum load - in mains operation: | 250 mA |
| Installation: | in device box in accordance with DIN 49073 |

Notes

- For installations in accordance with DIN VDE 0834.
 - DIN VDE 0834 states that components with a limited service life (rechargeable battery) must be replaced 1 x per year.
 - Please observe the regulations on the disposal of used batteries.
-

Scope of supply

- Blank cover plate is included with delivery.
 - Rechargeable battery included with delivery.
-