

Pushbutton sensor 4.95, 24 V 4-gang

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
white	5054 003	1	97.70	02	4010337074922
anthracite	5054 028	1	97.70	02	4010337074939

Features

- Pushbutton sensor 4.95 for connection to 24 V control systems.
- Pushbutton sensor 4.95 must be completed with rocker sets to be ordered separately.
The operating surfaces of the rocker sets are made of high-quality three-millimetre thick real material such as glass, stainless steel or aluminium.
- Two white status LEDs per rocker.
- Measurement of the room temperature with integrated temperature sensor (PT1000).

Technical data

Button	
- Rated voltage:	AC/DC 24 V SELV
- Current capacity:	20 mA per button
- Output resistance:	880 Ω
LED	
- Rated voltage:	DC 24 V SELV
- Current consumption:	approx. 1 mA per LED
Temperature sensor:	PT1000, class B
Protection class:	III
Installation depth:	16 mm
Ambient temperature:	-5 °C to +45 °C

Notes

- Suitable for SELV circuits only.
 - Professional inscription by the Gira inscription service www.marking.gira.com.
-

Scope of supply

- The pushbutton sensor is delivered with a program-neutral start-up rocker. The suitable rocker set for the switch range must be ordered separately.
-