

**eNet wireless switching/momentary-contact actuator  
1-gang, Mini zero-voltage**

| Specification | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---------------|-----------|--------------|------------------------|----|---------------|
|               | 5424 00   | 1/5          | 97.80                  | 42 | 4010337774211 |

**Features**

- The eNet radio switching/momentary-contact actuator enables switching of lighting.
- Operating modes: Switching actuator or momentary-contact actuator.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Can be set with eNet server:

- Flashing function.
- Delay time.
- Switch-on/off delay.
- Switch-off pre-warning.
- Minimum switching repeat time.
- Permanent-on, permanent-off.
- Repeater function.
- Localisation of the device.

**Technical data**

|                                     |                    |
|-------------------------------------|--------------------|
| Rated voltage:                      | AC 230 V, 50/60 Hz |
| Standby:                            | max. 0.5 W         |
| Ambient temperature:                | -25 °C to +70 °C   |
| Breaking capacity 230 V AC:         | 16 A/AC1           |
| Connected load                      |                    |
| - Light bulbs:                      | 2300 W             |
| - HV halogen lamps:                 | 2000 W             |
| - Wound electronic transformer:     | 1000 VA            |
| - Tronic transformer:               | 1500 W             |
| - Fluorescent lamps, uncompensated: | 920 VA             |

|                             |                        |
|-----------------------------|------------------------|
| - LED lights:               | typically 500 W        |
| - Compact fluorescent lamp: | typically 500 W        |
| - Capacitive load:          | 690 VA (560 µF)        |
| Connection cross section:   | Max. 4 mm <sup>2</sup> |
| Wireless frequency:         | 868.0 to 868.6 MHz     |
| Range (free field):         | approx. 100 m          |
| Dimensions:                 | Ø 53,0 H 28,0 mm       |

---

## Notes

- Mounting in device box, surface-mounted housing or in installation adapter.
-